

# HEAT STROKE PREVENTION METER

**NEW**



## Professional WBGT Monitor 87782/87785


- Check Indoor/Outdoor WBGT, TA/TG/RH & wind speed
- Designed with capacitance type humidity sensor with dust filter to get accurate reading and extend sensor life time
- Model 87785 is equipped with cup type anemometer to measure wind speed from all direction
- Audible beeper and backlight for danger zone warning



Wind speed value makes your WBGT more close to real climate thermo impact!



Model	87785	87782
Windspeed range	0.5~10 m/s	
Windspeed Acc.	+/- (2% of reading +0.2) m/s	
Temp. range	0~50°C	
Temp. resolution	0.1°C/°F	
Temp. accuracy	+/-0.6°C	
Humidity. range	0.1%~99.9%RH	
Humidity resolution	0.1%RH	
Humidity accuracy	+/-3%RH (at 25°C, 10~90%RH, others +/-5%RH)	
Globe Temp.(inside black ball)	0~80°C	
Globe Temp. Acc.	Indoor: +/-1°C (at 15~40°C), others 1.5°C outdoor: +/-1.5°C (at 15~40°C), others 2°C	
WBGT temp. range	0~50°C	
WBGT Alarm Range	20~50°C	
Black ball size(mm)	Dia. 75, height:75	
Stabilization time	15 ~25 minutes typical	
RH% Self calibration	YES	
Battery life	~100hour	
LCD size (mm)	50(H)x32(W)	
Operation temp.	0~50°C	
Operation RH%	Humidity < 80%	
Storage temp.	-20~50°C	
Storage RH%	Humidity < 90%	
Dimension(mm)	310(H)x91(diameter, windcup)	302(H)x75(W)x36.7(T)
Weight	~350g	~300g
Battery	AAA x4pcs	
Standard Package	Meter/Battery/Manual/Hard carry case (87785) or paper box (87782)	



WBGT	Flag	Activity Intensity
< 80°F < 26.7°C	White	Normal activity. Caution should be taken.
80-84.9°F 26.7-29.4°C	Green	Discretion is required in planning intense physical activity.
85-87.9°F 29.4-31°C	Yellow	Intense activity for new and acclimatized persons should be curtailed.
88-89.9°F 31-32.2°C	Red	Intense exercise must be curtailed for those with less than 12 weeks training in hot weather. Be on high alert
> 90°F > 32.2°C	Black	Cancel all outdoor exercise.

**Ordering Code** Source: Manual of Naval Preventive Medicine (NAVMED P-5010)  
**VZ87782AZ, 87782 meter**  
**VZ87785AZ, 87785 meter**  
**VZ87781ST2, salt bottles**  
**VZUSBAZM, software kit**

### Optional



**CAL. SALT BOTTLE**  
P/N: VZ87781ST2  
(33% & 75%)  
For 87782/87785  
Calibration .



**USB cable & software**  
P/N: VZUSBAZM